

Price List Addendum

EFFECTIVE August 23, 2021

Fire Protection Valves and Devices

Universal Manifold Check Valve

SERIES UMC

Includes Series UTD Test and Drain, and Series ARV Adjustable Relief Valve.

Refer to publication 30.72.



SERIES UMC – UNIVERSAL MANIFOLD CHECK VALVE

UMC Body Size			
Nominal inches	Description	Part Code	Price Each
1¼	GxG Right Handed with Control Valve and Hose	Y317843RVH	\$1473.50
	GxG Right Handed with Hose	Y0317843RH	1286.00
	GxG Left Handed with Control Valve and Hose	Y317843LVH	1473.50
	GxG Left Handed with Hose	Y0317843LH	1286.00
1½	GxG Right Handed with Control Valve and Hose	Y317844RVH	1539.00
	GxG Right Handed with Hose	Y0317844RH	1321.50
	GxG Left Handed with Control Valve and Hose	Y317844LVH	1539.00
	GxG Left Handed with Hose	Y0317844LH	1321.50
2	GxG Right Handed with Control Valve and Hose	Y317806RVH	1707.50
	GxG Right Handed with Hose	Y0317806RH	1456.00
	GxG Left Handed with Control Valve and Hose	Y317806LVH	1707.50
	GxG Left Handed with Hose	Y0317806LH	1456.00
2½	GxG Right Handed with Control Valve and Hose	Y317809RVH	1738.50
	GxG Right Handed with Hose	Y0317809RH	1487.50
	GxG Left Handed with Control Valve and Hose	Y317809LVH	1738.50
	GxG Left Handed with Hose	Y0317809LH	1487.50
3	GxG Right Handed with Control Valve and Hose	Y317812RVH	2008.50
	GxG Right Handed with Hose	Y0317812RH	1791.00
	GxG Left Handed with Control Valve and Hose	Y317812LVH	2008.50
	GxG Left Handed with Hose	Y0317812LH	1791.00
4	GxG Right Handed with Control Valve and Hose	Y317817RVH	2146.00
	GxG Right Handed with Hose	Y0317817RH	1931.00
	GxG Left Handed with Control Valve and Hose	Y317817LVH	2146.00
	GxG Left Handed with Hose	Y0317817LH	1931.00
6	GxG Right Handed with Control Valve and Hose	Y317818RVH	2663.00
	GxG Right Handed with Hose	Y0317818RH	2325.00
	GxG Left Handed with Control Valve and Hose	Y317818LVH	2663.00
	GxG Left Handed with Hose	Y0317818LH	2325.00
8	GxG Right Handed with Control Valve and Hose	S080UMCRV0	4026.00
	GxG Right Handed with Hose	S080UMCR00	3259.50

NOTE: Items listed in shaded areas are non-cancellable and non-returnable.



TERMS AND CONDITIONS OF SALE

Victaulic published Terms and Conditions of Sale listed in General Price List will apply. Prices, Designs and Conditions of Sale are subject to change without notice.

P.O. Box 31, Easton, PA 18044-0031 • 4901 Kesslersville Road, Easton, PA 18040 • 1-800-PICK-VIC (1-800-742-5842) • 1-610-250-8817 (fax) • pickvic@victaulic.com